

CX-MA0611 & CX-MA1211 Glass Door Mounting Kit for 600 and 1200 LB Magnetic Locks


INSTALLATION INSTRUCTIONS

1. INSTALLING THE U-BRACKET

- 1. Place the U-rubber over the top of the glass door as shown in figure 1
- 2. Place the insert plate against the rubber (On the side where the armature plate will sit)
- 3. Place the U-Bracket over the insert plate and tighten using the 4 set screws provided
- 4. Place the flat washers in between the bracket unit and the armature plate. Secure the bracket unit by tightening the Armature plate with the Philips flat head screw provided

Note: DO NOT attach the mounting bracket too firmly, allow floating movement for maximum holding force.

CX-MA0611 and CX-MA1211 Bracket (Frameless Glass Door Installtion)








figure 1 Installation Method

2. DIMENSIONS



CX-MA0611 Bracket



CX-MA1211 Bracket



Opening New Doors to Innovation, Quality and Support! Visit: www.camdencontrols.com

Call: 1.877.226.3369 / 905.366.3377



File: CX_MA0611&CX-MA121_Glass-DoorMounting_ForMagLocks.indd Revised: December 22nd 2021 Part No.: 40-82B294